

# PHILIPS

Olas Fan Ceiling Light  
35 (Fan) + 24 (Light) W

Fan Ceiling Lights

3,000–6,500 K

Black

Dimmable; MultiColour  
Temperature; Remote  
Control; Tunable White

8721103096128



## Powerful and quiet airflow with tunable LED light

The Philips Olas ceiling fan with LED light will keep your indoor spaces bright, comfortable and stylish all day and all year. With permanently extended blades, a generous airflow and two airflow directions, our ceiling fan offers consistent performance, cooling quickly in the summer and circulating the air effectively in the winter. The whisper-quiet motor won't disturb your sleep or concentration, while the stable ceiling mount and perfectly weight-balanced fan blades minimise wobbling, keeping you safe and avoiding ceiling cracks. The light itself offers the high light quality and adaptability that you've come to expect from Philips. Create the perfect ambience for every moment with smooth dimming (down to 5%) and tunable white light from warm white (3,000 K) to cool daylight (6,500 K). Our upgraded RF-based remote control lets you easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan.

### Premium quality

- Quiet operation

### Control

- Seamlessly adjustable ambience
- Intuitive remote control

**Durability**

- Powerful airflow
- Adjustable fan speed
- Two airflow directions

**Safety and durability**

- Safe and stable

# Highlights

## Quiet operation

Quiet DC motor (<50 dB – less than a refrigerator hum) won't disrupt your sleep or distract you when you need to concentrate; stable ceiling mount minimises wobbling

## Seamlessly adjustable ambience

Philips ceiling fans with LED lights offer smooth dimming down to 5%, tunable white light ranging from warm white (3,000 K) to cool daylight (6,500 K), letting you create the perfect ambience for every moment

## Intuitive remote control

With an intuitive RF-based remote control, you can easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan

## Powerful airflow

Our ceiling fan cools fast and effectively with a robust DC motor, optimised fan blade design with powerful airflow

## Adjustable fan speed

The Philips ceiling fans let you choose from six fan speeds, allowing you to match the airflow exactly to your activities or the seasons

## Two airflow directions

DC motor allows forwards and backwards airflow directions for year-round usage: cooling in the summer, warm air circulation in the winter

## Safe and stable

Stable ceiling mount and bearings, along with perfectly weight-balanced fan blades, minimise wobbling, ensure safety and avoid cracked ceilings

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: Black
- Material: Metal

## Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2
- Luminous efficacy (rated) (nom.): 110

## Miscellaneous

- Especially designed for: Bedroom, Living Room
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, MultiColour Temperature, Remote control, Tunable White

**Other characteristics**

- Lamp current: 280 mA
- Fan Flow: 10,440 m<sup>3</sup>/h
- Fan efficiency: 298

**Product dimensions and weight**

- Net weight: 5.5 kg
- Overall height: 31 mm

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Diameter: 1,320 mm
- Total lumen output fixture: 2650@4300K
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 8721103096128
- Net weight: 5.5 kg
- Gross weight: 7.9 kg
- Height: 25.4 cm
- Length: 67.7 cm
- Width: 35.7 cm



Issue date: 2026-04-15  
Version: 0.191

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)