

PHILIPS

Solr Fan Ceiling
Light

Fan Ceiling Lights

2,700–5,500K

White

Dimmable; Remote Control;
Tunable White

8721103103130



Retractable-blade ceiling fan with dimmable and tunable LED light

The Philips [Tyr] /Solr] retractable-blade ceiling fan with LED light will brighten up your indoor spaces while offering a cooling airflow. Choose from six fan speeds, up to a maximum airflow volume of 150 m³/min, to match whatever you have going on at home. Two-sided fan blades are made of robust plywood and keep their shape without deformation even after thousands of hours of use. Simply flip the fan blades to change the colour – from white to light wood or from black to dark wood. Instantly change the ambience with smooth dimming down to 10% and three shades of white light: warm white (2,700 K), cool white (4,000 K) and cool daylight (5,500 K). Our upgraded RF-based remote control lets you easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan.

Premium quality

- Quiet operation

Control

- Intuitive remote control
- Dimmable with three shades of white light

Durability

- Powerful airflow
- Adjustable fan speed
- Two airflow directions

Safety and durability

- Safe and built to last

Highlights

Quiet operation

Quiet DC motor (<50 dB – less than a refrigerator hum) won't disrupt your sleep or distract you when you need to concentrate; stable ceiling mount minimises wobbling

Intuitive remote control

With an intuitive RF-based remote control, you can easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan

Dimmable with three shades of white light

These Philips ceiling fans with LED lights offer smooth dimming down to 10%; choose warm white light (3,000 K), cool white light (4,300 K) or cool daylight (6,500 K), letting you choose the right ambience for every moment

Powerful airflow

Our ceiling fan cools fast and effectively with a robust DC motor, optimised fan blade design with powerful airflow

Adjustable fan speed

The Philips ceiling fans let you choose from six fan speeds, allowing you to match the airflow exactly to your activities or the seasons

Two airflow directions

DC motor allows forwards and backwards airflow directions for year-round usage: cooling in the summer, warm air circulation in the winter

Safe and built to last

Install your Philips ceiling fan with LED light once and enjoy years of safe, worry-free comfort; complies with international safety standards to protect you from shocks, fire and daily use

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700-5500
- Warm-up time to 60% light: <2
- Luminous efficacy (rated) (nom.): 128

Miscellaneous

- Especially designed for: Bedroom, Living Room
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Remote control, Tunable White

Other characteristics

- Lamp current: 330 mA
- Fan Flow: 7,980 m³/h
- Fan efficiency: 249

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 5.3 kg
- Overall height: 38 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 4500 @4000K
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20
- Class of protection: Class I – Earthed

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103103130
- Net weight: 5.3 kg
- Gross weight: 8.9 kg
- Height: 29.4 cm
- Length: 55.7 cm
- Width: 55.7 cm



Issue date: 2026-05-19
Version: 0.244

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com