

PHILIPS

Civx Fan Ceiling Light
32 (Fan) + 24 (Light) W

Fan Ceiling Lights

3000/4300/6500K

Black

Remote
Control; SceneSwitch; Tunable
White

8721103103178



Quiet airflow with warm to cool white light

The Philips [Velyx/Civx] ceiling fan with LED light will brighten up your indoor spaces while offering a cooling airflow. Choose from six fan speeds, up to a maximum airflow volume of 150 m³/min, to match whatever you have going on at home. Two-sided fan blades are made of robust plywood and keep their shape without deformation even after thousands of hours of use. Simply flip the fan blades to change the colour – from white to light wood or from black to dark wood. Instantly change the ambience with smooth dimming down to 10% and three shades of white light: warm white (3,000 K), cool white (4,500 K) and cool daylight (6,500 K). Our upgraded RF-based remote control lets you easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan.

Easy to experience

- Two-sided blade

Control

- Dimmable with three shades of white light

Durability

- Two airflow directions
- Comfortable airflow

Safety and durability

- Keeps original blade shape
- Safe and built to last

Highlights

Two-sided blade

Choose blades with white and light wood sides or black and dark wood sides; flip the blades for an instant colour change

Dimmable with three shades of white light

These Philips ceiling fans with LED lights offer smooth dimming down to 10%; choose warm white light (3,000 K), cool white light (4,300 K) or cool daylight (6,500 K), letting you choose the right ambience for every moment

Two airflow directions

DC motor allows forwards and backwards airflow directions for year-round usage: cooling in the summer, warm air circulation in the winter

Comfortable airflow

Our ceiling fan cools fast and effectively with a robust DC motor and a maximum airflow volume of 170 m³/min

Keeps original blade shape

Blades are made of robust plywood, keeping their original shape and avoiding deformation after thousands of hours of use

Safe and built to last

Install your Philips ceiling fan with LED light once and enjoy years of safe, worry-free comfort; complies with international safety standards to protect you from shocks, fire and daily use

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: Black
- Material: Metal

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 3000–4300–6500 K
- Warm-up time to 60% light: <2
- Luminous efficacy (rated) (nom.): 104

Miscellaneous

- Especially designed for: Bedroom, Living Room
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Remote control, SceneSwitch, Tunable White

Other characteristics

- Lamp current: 260 mA
- Fan Flow: 10,200 m³/h
- Fan efficiency: 318

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 4.3 kg
- Overall height: 34 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 1,320 mm
- Total lumen output fixture: 2500@4300K
- Bulb technology: LED
- Light colour: Tunable white (warm white, natural white and cool white on switch toggle)
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC – product: 8721103103178
- Net weight: 4.3 kg
- Gross weight: 4.3 kg
- Height: 19.9 cm
- Length: 27.6 cm
- Width: 65.5 cm



Issue date: 2026-04-15
Version: 0.246

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com