

PHILIPS

Splay Wall Lights
4.3W

Ultra Efficient

2700 K

Anthracite

Water Resistant



8721103110039



Our most energy-efficient LED lights yet

The Philips Splay LED outdoor light in anthracite grey is made from durable die-cast aluminium. The design provides bi-directional light distribution to illuminate your wall with plenty of diffuse bright light. This Ultra Efficient outdoor lights use groundbreaking new technology to cut carbon emissions, reduce material waste and lower energy usage.

Sustainable light solutions

- Long lifetime up to 50,000 hours
- Ultra Efficient

Premium quality

- Durable design with PowerShield coating

Designed for outdoors

- IP44 – weatherproof

High-quality light

- Warm white light 2,700 K

Highlights

Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

Ultra Efficient



Consumes at least 50% less energy compared to equivalent standard LED lights from Philips.

Durable design




Protected by PowerShield To keep your outdoor lights in excellent condition, we use a high-performance powder coating powered by Interpon, an AkzoNobel brand. Tougher than traditional paints, it protects against fading, scratches, dents and rust for long-lasting beauty and performance.

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Warm white light 2,700 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces warm, relaxing light at 2,700 K.

Specifications

Bulb characteristics

- Dimmable: No

Design and finishing

- Colour: Anthracite
- Material: Aluminium

Durability

- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K

Miscellaneous

- Especially designed for: Garden and Patio, Garage
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED innovations: UltraEfficient
- Extra Features: Water Resistant

Power consumption

- Power: 4.3

Product dimensions and weight

- Net weight: 1.41 kg
- Overall height: 96 mm
- Overall length: 12 mm
- Overall width: 16 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 800
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: AC 220-240
- Energy class included light source: B
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I – Earthed
- Light source replaceable: No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103110039
- Net weight: 1.41 kg
- Gross weight: 1.96 kg
- Height: 104.5 cm
- Length: 13.5 cm
- Width: 17.5 cm



Issue date: 2026-04-15
Version: 0.160

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com