

# PHILIPS

## Wall Lights 10W

Outdoor Solar

7500K

Black

Solar

8721103119605



## Solar-powered garden light for all seasons

Weatherproof, high-quality materials for long-lasting automated light

### **Designed for outdoors**

- IP65 weatherproof rated

### **High-quality light**

- EyeComfort – light that's easy on your eyes

# Highlights

## IP65 weatherproof rated

An IP rating contains two digits which refer to protection against solids, such as dust, or liquids, such as rain. IP65 means that these light fixtures are protected against water splashed from any direction and are suitable for outdoor use.

## EyeComfort – light that's easy on your eyes



Poor-quality light can cause eye strain. With many people spending time

indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure that they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of its lifespan, delivering consistent light quality, output and colour for more than a decade.

# Specifications

## Bulb characteristics

- Dimmable: No

## Design and finishing

- Colour: Black
- Material: Plastic

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Centrepiece: No

## Light characteristics

- Colour rendering index (CRI):  $\geq 70$

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED innovations: EyeComfort
- Extra Features: Solar

## Power consumption

- Power: 10

## Product dimensions and weight

- Net weight: 1.336 kg
- Overall height: 11 mm
- Overall length: 29 mm
- Overall width: 5 mm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 800
- Bulb technology: LED
- Light colour: 7500
- Mains power: DC 4.2
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III – Safe Extra Low Voltage
- Light source replaceable: No

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8721103119605
- Net weight: 0.18 kg
- Gross weight: 0.24 kg
- Height: 12.2 cm
- Length: 14 cm
- Width: 5.7 cm



Issue date: 2026-05-13  
Version: 0.76

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)