

PHILIPS

Smart RGBIC LED Light Strip, 5 m, Type G, Connected by WiZ

Smart LED

Multicoloured light effects

Static and dynamic light modes

Versatile and cuttable



8721103136015



Colours that flow

This versatile RGBIC light strip delivers dazzling multicoloured effects – from chasing rainbows and smooth colour fades to sparkling dynamic scenes. Set the mood in any room using a wide range of static and dynamic light modes in vibrant colours. Designed for flexibility, the strip can be cut to fit almost any space, so you can install it easily on furniture, along walls or under cabinets (please note that cut-off pieces cannot be reattached). Easy to set up using the WiZ app and fully compatible with all Connected by WiZ products.

Easy setup

- Set-up couldn't be easier
- Easy to install

Smart features

- SpaceSense motion detection
- Sync with music

Smart devices

- Matter-certified

Light modes

- Multicoloured light
- Vibrant colour

Highlights

Set-up couldn't be easier




1. Download the WIZ app
2. Switch on your light
3. Connect the light to Wi-Fi

Easy to install



Bend and cut to fit any space, then use the double-sided adhesive backing and mounting accessories to secure in place.

SpaceSense motion detection




Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WIZ lights or devices.

Sync with music



Feel the rhythm with Music Sync. Effortlessly sync your lights with your favourite tunes using the microphone on your smartphone.

Vibrant colour




Choose from millions of vibrant colours to create ambient lighting to suit any mood.

Matter-certified



Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

Multicoloured light



This light strip can produce various colours simultaneously for dazzling multicoloured light effects, like chasing rainbows and sparkles.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your colour: Yes
- Dimmable with remote control: Yes
- Fully weatherproof: No
- LED integrated: Yes
- On/off switch on wire: Yes
- Power adapter included: Yes
- Remote control included: No
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Colour rendering index (CRI): ≥ 80
- Colour temperature: 2200-6500 K
- Warm-up time to 60% light: < 2
- Luminous efficacy (rated) (nom.): 95

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Living Room, Children's room, Entertainment room

Other characteristics

- Lamp current: 75 mA

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Power: 15.3
- Energy consumption kWh/1,000 hours: 11

Product dimensions and weight

- Net weight: 0.22 kg
- Overall height: 0.21 mm
- Overall length: 500 mm
- Overall width: 1 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50-60
- Total lumen output fixture: NA
- Bulb technology: LED
- Light colour: Gradient coloured light (RGBIC)
- Wattage bulb included: 18
- IP code: IP20
- Class of protection: Class II – Double Insulated

The bulb

- Software upgradable: Yes

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 8721103136015
- Net weight: 0.22 kg
- Gross weight: 0.31 kg
- Height: 16.7 cm
- Length: 8.2 cm
- Width: 13.9 cm



Issue date: 2026-06-13
Version: 0.213

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com