

PHILIPS

Pedestal/Pathway
Lights 0.85W

Outdoor Solar

RGBW (3000)

Black

Water Resistant

8721103139917



Solar-powered garden light for all seasons

Long-lasting solar light that saves you money

Ease of use

- A full range of available applications

Decorate your garden with light

- Opt for pedestal lights

Highlights

A full range of available applications

Ideal outdoor lighting for a garden, terrace, pathway or balcony, Philips outdoor wall, post, pedestal and ceiling lights create a cosy, relaxing atmosphere when the sun goes down, as well as providing the reassurance of being able to see safely after dark.

Opt for pedestal lights



Enhance your outdoor space with this pedestal lamp, the perfect lighting for your garden, the edge of your terrace or as illumination for a driveway or path.

Specifications

Bulb characteristics

- Dimmable: No

Design and finishing

- Colour: Black
- Material: Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: Yes
- Centrepiece: No

Light characteristics

- Colour rendering index (CRI): 70

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Pedestal/Pathway Lights
- EyeComfort: No
- LED innovations: EyeComfort
- Extra Features: Water Resistant

Power consumption

- Power: 0.85

Product dimensions and weight

- Net weight: 0.33 kg
- Overall height: 24 mm
- Overall length: 11 mm
- Overall width: 10 mm

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 80
- Bulb technology: LED
- Light colour: RGBW (3000)
- Mains power: DC 4.2
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III – Safe Extra Low Voltage
- Light source replaceable: No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103139917
- Net weight: 0.66 kg
- Gross weight: 0.81 kg
- Height: 12 cm
- Length: 19.5 cm
- Width: 15.1 cm



Issue date: 2026-05-13
Version: 0.72

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com