

# PHILIPS

Amigo Fan Ceiling Light  
40 (light) + 20 (fan) W


Fan Ceiling Lights

2700-6500K

White

Dimmable; Remote Control; RGB  
Colours; Tunable White

8721103145710



## Sturdy ceiling fan with dimmable and tunable LED light

The Philips Amigo ceiling fan with LED light will keep your indoor spaces bright, comfortable and colourful all day and all year. With curved blades enclosed in a sturdy double-ring housing for safe and reliable operation, a maximum airflow volume of 30m<sup>3</sup>/min, six fan speeds and two airflow directions, our ceiling fan cools quickly in the summer and circulated the air effectively in the winter. The whisper-quiet motor won't disturb your sleep or concentration, while the streamlined blade design reduces wind noise. Create the perfect ambience with nine colour modes, including six dynamic full-colour modes and tunable white light from warm (2,700 K) to cool (6,500 K). Our upgraded RF-based remote control lets you easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan.

### **Vary your ambience with coloured light**

- Colourful and dynamic light scenes

### **Premium quality**

- Quiet operation

### **Control**

- Intuitive remote control

**Durability**

- Adjustable fan speed
- Two airflow directions
- Comfortable airflow

**Safety and durability**

- Strong and safe

# Highlights

## Colourful and dynamic light scenes

Change the ambience to match all your activities at the touch of a button, 9 colour modes includes 8 dynamic light shows and tunable white light from a warm 2,700 K to a cool 6,500 K

## Quiet operation

Quiet DC motor (<50 dB – less than a refrigerator hum) won't disrupt your sleep or distract you when you need to concentrate; stable ceiling mount minimises wobbling

## Intuitive remote control

With an intuitive RF-based remote control, you can easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan

## Adjustable fan speed

The Philips ceiling fans let you choose from six fan speeds, allowing you to match the airflow exactly to your activities or the seasons

## Two airflow directions

DC motor allows forwards and backwards airflow directions for year-round usage: cooling in the summer, warm air circulation in the winter

## Comfortable airflow

Our ceiling fan cools fast and effectively with a robust DC motor and a maximum airflow volume of 170 m<sup>3</sup>/min

## Strong and safe

The sturdy double ring design is stronger and safer than the single-ring structures used in other ceiling fans, with easy twist-and lock installation

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700-6500 K
- Warm-up time to 60% light: <2
- Luminous efficacy (rated) (nom.): 110

## Miscellaneous

- Especially designed for: Bedroom, Living Room
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Remote control, RGB Colours, Tunable White

## Other characteristics

- Lamp current: 300 mA
- Fan Flow: 1,620 m<sup>3</sup>/h
- Fan efficiency: 81

### Product dimensions and weight

- Net weight: 2 kg
- Overall height: 15 mm

### Service

- Warranty: 5 year(s)

### Technical specifications

- Diameter: 480 mm
- Total lumen output fixture: 4400 @ 4000K
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8721103145710
- Net weight: 1.5 kg
- Gross weight: 2.32 kg
- Height: 51.7 cm
- Length: 51.7 cm
- Width: 18.7 cm



Issue date: 2026-04-15  
Version: 0.65

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)