

PHILIPS

Smart LED GU10 Kit, Full Colour, Tunable White, White, 3-Pack

Smart LED

Tunable white and coloured light

Bulb, ring fitting and connector included

Head tiltable to 30°



8721103148421



Highlight your home

Upgrade your lighting with this smart LED GU10 kit, offering tunable white light from warm, relaxing tones to cooler, focus-enhancing hues (2,200 K–6,500 K), as well as vibrant colours for decorative and ambient lighting. Smooth dimming from full brightness down to 1% lets you set the perfect mood at any time.

Easy setup

- Set-up couldn't be easier
- Easy installation

Smart control

- The smarter way to light your home

Smart features

- Automate your light with schedules

Smart devices

- Matter-certified

Light modes

- Tunable warm to cool white and preset modes
- Bright and vivid colours

Highlights

Set-up couldn't be easier



1. Download the WIZ app
2. Switch on your light
3. Connect the light to Wi-Fi

Easy installation



Simply remove the metal ring, insert and connect the bulb, then reattach the metal ring to secure in place.

The smarter way to light your home



The kit includes everything you need to start enjoying the benefits of smart lightning.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Matter-certified



Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

Tunable warm to cool white and preset modes



Choose from a wide range of energising cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Bright and vivid colours



Decorate your home and set the mood for any occasion using bright light in vibrant colours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Extra feature/accessory incl.

- Adjustable spot head: Yes
- Choose your colour: Yes
- Dimmable with remote control: Yes
- Fully weatherproof: No
- LED integrated: Yes
- Remote control included: No
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Beam angle: 36
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2200-6500 K
- Warm-up time to 60% light: <2
- Luminous efficacy (rated) (nom.): 85

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room
- EyeComfort: No

Other characteristics

- Lamp current: 40 mA

Power consumption

- Voltage: 220-240 V
- Energy consumption kWh/1,000 hours: 11

Product dimensions and weight

- Net weight: 0.155 kg
- Cut out length: 6.8-7.5 cm
- Cut out width: 6.8-7.5 cm
- Recessed distance: 10 mm
- Overall height: 7.2 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50/60
- Diameter: 90 mm
- Total lumen output fixture: 400
- Bulb technology: LED
- Light colour: Coloured and white light (RGBW)
- Wattage bulb included: MAX 5 LED GU10
- IP code: IP20
- Class of protection: Class II – Double Insulated

The bulb

- Form factor: NA
- Software upgradable: Yes

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 8721103148421
- Net weight: 0.16 kg
- Gross weight: 0.61 kg
- Height: 10.6 cm
- Length: 13.1 cm
- Width: 20.8 cm



Issue date: 2026-07-04
Version: 0.100

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com