

PHILIPS

Mycena portable light

Portable Lights

4,000/3,000/6,500K

Beige

Dimmable; Multicolour temperature

8721103148483



Decorate with portable light

This minimalist table lamp features a rechargeable 1,800 mAh battery that delivers up to 6 hours of reliable, cordless lighting without a drop in performance. Emitting a consistent 150 lumens (LED light source 200 lm), it provides the perfect level of brightness for relaxing evenings or creating a cosy atmosphere. With selectable white light options – cool 6,500 K, neutral 4,000 K and warm 3,000 K – you can easily tailor the mood to suit any room, from living rooms and bedrooms to kitchens. Intuitive touch controls make operation effortless: simply tap to swap between light tones or long-press to adjust the brightness.

High-quality light

- EyeComfort – light that's easy on your eyes

Match your interior

- Expressive and elegant form
- Available in three colour options

Control

- Dimmable

Highlights

EyeComfort – light that's easy on your eyes



Poor-quality light can cause eye strain. With many people spending time

indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure that they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of its lifespan, delivering consistent light quality, output and colour for more than a decade.

Available in three colour options

Choose the right colour to match your existing colour schemes.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light to a cosy glow – just like traditional lamps.

Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: Beige
- Material: Metal, Plastic

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 3000/4000/6500
- Warm-up time to 60% light: <2
- Luminous efficacy (rated) (nom.): 75

Miscellaneous

- Especially designed for: Bedroom, Living Room
- Style: Contemporary
- Type: Portable Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, MultiColour Temperature

Other characteristics

- Lamp current: 400 mA

Product dimensions and weight

- Net weight: 0.36 kg
- Overall height: 204 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 156 mm
- Total lumen output fixture: 150
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: DC 5
- Battery type: INR18650
- IP code: IP20
- Class of protection: Class III – Safe Extra Low Voltage

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC – product: 8721103148483
- Net weight: 0.36 kg
- Gross weight: 0.44 kg
- Height: 21.4 cm
- Length: 18 cm
- Width: 18 cm



Issue date: 2026-07-11
Version: 0.111

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com