

# PHILIPS

Gradient Floor Light,  
RGBIC LED, Connected  
by WiZ

Smart LED

Multicoloured light effects

Static and dynamic light modes

Sync with TV  
(hardware required)



8721103160720



## Splashes of colour

Transform your space with this gradient floor light. RGBIC technology produces vibrant light effects in multiple colours at once. With a sleek, minimalist design, it looks great in any room, while customisable preset modes let you choose between dynamic animations or soft, static glows. You can even sync your light with your TV screen (syncing hardware required) or make them dance to the beat of your favourite songs.

### Easy setup

- Set-up couldn't be easier

### Smart features

- SpaceSense motion detection
- Sync with music

### Smart devices

- Matter-certified

### Light modes

- Smooth gradients
- Immersive lighting

### Form factor

- Stylish design


# Highlights

## Set-up couldn't be easier



1. Download the WiZ app  
2. Switch on your light  
3. Connect the light to Wi-Fi

## SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WiZ lights or devices.

## Sync with music




Feel the rhythm with Music Sync. Effortlessly sync your lights with your favourite tunes using the microphone on your smartphone.

## Matter-certified




Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

## Smooth gradients



Wash the walls with multiple colours simultaneously, blended smoothly to create beautiful light gradient effects.

## Immersive lighting



Transform your home entertainment experience by syncing your lights with music and video – syncing hardware required.

## Stylish design



This lamp's modern, minimalist style blends effortlessly into any space, bringing a touch of sophistication and elegance to your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: Black
- Material: Plastic, Aluminium

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your colour: Yes
- Dimmable with remote control: Yes
- Fully weatherproof: No
- LED integrated: Yes
- On/off switch on wire: No
- Remote control included: No
- Solar Energy: No
- Warm glow dimmable light: No

## Light characteristics

- Colour rendering index (CRI):  $\geq 80$
- Colour temperature: 2700/6500
- Warm-up time to 60% light:  $< 2$

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Children's room, Entertainment room

## Other characteristics

- Lamp current: 69 mA

## Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Energy consumption kWh/1,000 hours: 9.5

## Product dimensions and weight

- Net weight: 1.347 kg
- Overall length: 135.5 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50-60
- Diameter: 90 mm
- Total lumen output fixture: NA
- Bulb technology: LED
- Light colour: Gradient coloured and white light (RGBICW)
- Wattage bulb included: 9.7
- IP code: IP20
- Class of protection: Class II – Double Insulated

## The bulb

- Software upgradable: Yes

## What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

## Packaging dimensions and weight

- EAN/UPC - product: 8721103160720
- Net weight: 1.35 kg
- Gross weight: 3.03 kg
- Height: 14.8 cm
- Length: 143.4 cm
- Width: 14.3 cm



Issue date: 2026-06-13  
Version: 0.57

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)