

PHILIPS

SuperSlim Ceiling LED
Light, Tunable White Light
2,700 K to 6,500 K, 32W

Smart LED

Super-slim design

Tunable white
light 2,700-6,500 K

Low dimming to 1%



8721103163578



Create moments with whites

This round ceiling light is an excellent choice for spaces with low ceilings. Its slim 32 mm frame helps create a clean, modern look without overwhelming the room. The sleek design not only enhances the aesthetic appeal but also allows for easy mounting on ceilings where recessed installation isn't possible. Easily set the mood with a dimmable smart LED ceiling light that can produce tunable white (2,700 K to 6,500 K). Easy to set up and control using the WiZ app and fully compatible with all Connected by WiZ products.

Smart control

- Smart controls

Smart features

- Automate your light with schedules
- SpaceSense motion detection

Smart devices

- Matter-certified

Light modes

- Tunable white light
- Always the right light
- Instant cosy vibes

Highlights

Smart controls

Take full control using the WIZ app or voice commands via your smart home assistant.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WiZ lights or devices.

Matter-certified



Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

Tunable white light

Easily adjust from cool, blueish hues that enhance visibility and focus to soft, warmer tones for relaxing (CCT range 2,700 K-6,500 K).

Always the right light

Easily set the mood for any activity with preset light modes like Relax and Focus.

Instant cosy vibes

Dim to warm makes your light softer as it dims to effortlessly create a cosy atmosphere.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your colour: Yes
- Dimmable with remote control: Yes
- Fully weatherproof: No
- LED integrated: Yes
- Remote control included: No
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): ≥ 80
- Colour temperature: 2700/6500
- Warm-up time to 60% light: < 2
- Luminous efficacy (rated) (nom.): 95

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room, Study
- EyeComfort: Yes

Other characteristics

- Lamp current: 75 mA

Power consumption

- Power factor: 0.9
- Voltage: 220–240 V
- Energy consumption kWh/1,000 hours: 11

Product dimensions and weight

- Net weight: 2.3 kg
- Overall height: 2.8 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50–60
- Diameter: 550 mm
- Total lumen output fixture: 3800
- Bulb technology: LED
- Light colour: Tunable white light
- Wattage bulb included: 32
- IP code: IP20
- Class of protection: Class II – Double Insulated

The bulb

- Software upgradable: Yes

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC – product: 8721103163578
- Net weight: 2.3 kg
- Gross weight: 2.65 kg
- Height: 55 cm
- Length: 3.2 cm
- Width: 54.5 cm



Issue date: 2026-06-17
Version: 0.155

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com