



Smart lighting for you daily living

Fashion concise line draw the outline of the environment light path. In order to create a high quality space with Non-center Piece design, Philips launches brand new Magnetic Sys products. With the unique patent GentleBright technology, using professional 2-zone diffuser design to precise control of light, filter stray light effectively, reduce glare and bring comfortable and bright pure light! Recessed trimless tracker can be collocated with high flexibility, multi-module application adapt to unlimited installation scenario, which shows off fashion versatile highlight exclusive sense of life, leading contemporary fashion lighting, and decorate the beauty of modern space!

Designed for your living- and bedroom

· Create a stylish and welcoming atmosphere

Match your interior

Super slim design

Light effect

· Bright light with uniform distribution

Highlights

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Specifications

Bulb characteristics

· Intended use: Indoor

Design and finishing

· Color: Black

Material: Metal, PlasticHousing Color: Black

Housing Material: Metal—Plastic
 Option Lagrange Fraids Taylored

Optical cover finish: Textured

• Optical cover material: Polycarbonate

Durability

· Number of switch cycles: 12,500

• Ambient temperature range: -20 to +40 °C

· Nominal lifetime: 25,000 hour(s)

Extra feature/accessory incl.

· Adjustable spot head: Yes

• Dimmable with remote control: No

· LED integrated: Yes

Remote control included: No

Guarantee

· Warranty period: 1 years

Light characteristics

• Beam angle: 24 degree(s)

· Color consistency: 5 SDCM

· Color rendering index (CRI): 90

· Luminous flux tolerance: +/-10%

· Constant light output: No

 Correlated Color Temperature (Nom): 4000

Initial chromaticity: ((, 0.3818, 0.3833)) < 5

· Light source replaceable: Yes

· Luminaire light beam spread: 24°

· Luminous Flux: 740 lm

· Optic material: Polycarbonate

· Optic type: Beam angle 24°

· Reflector material: Polycarbonate

 Luminous Efficacy (rated) (Nom): 77.00 lm/W

Miscellaneous

 Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway

Style: Contemporary

Type: Track Lights

EyeComfort: Yes

Other characteristics

· Lamp current: 200 mA

• EU RoHS compliant: Yes

Power

· Input Voltage: 48

• Power Factor (Fraction): -

Power consumption

Power Consumption: 9.5

• Power consumption tolerance:

+/-10%

Product dimensions and weight

Net weight: 0.175 kgHeight: 18.6 cmLength: 16.3 cmWidth: 4.2 cm

Overall height: 186 mmOverall length: 163 mmOverall width: 42 mm

Service

Warranty: 3 year(s)

Technical specifications

· Total lumen output fixture: 740

Light color: 4000Mains power: 48

Wattage bulb included: 9.5
IP code: IP20 | Finger-protected
Class of protection: Class III - Safe

Extra Low Voltage

· Connection: Connection unit 2-pole

· Dimmable: No

 Driver/power unit/transformer: Power supply unit external (On/Off)

· Driver included: No

· Fixation material: Polyamide

 Flammability mark: For mounting on normally flammable surfaces

 Glow-wire test: Temperature 650 °C, duration 30 s

 Ingress protection code: IP20 | Finger-protected

· Line Frequency: -

• Mech. impact protection code: IK03 |

0.3 J

· Number of gear units: 1 unit

Suitable for random switching: NoProtection class IEC: Safety class III

Packaging dimensions and weight

• EAN/UPC - product: 6922341954979

Net weight: 0.17 kgGross weight: 0.21 kg

Height: 19 cmLength: 5.5 cmWidth: 12.5 cm



Issue date: 2025-08-30 Version: 0.163 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips