

# PHILIPS

Ceiling Light 17W

Ceiling Lights

4000K

White

6922341982286



## Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes

### Light effect

- This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

### Easy to experience

- Easy installation

### Light effect

- Uniform light distribution

### Premium quality

- Easy to clean

# Highlights

## Interlaced Optics

This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

## Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

## Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

## Uniform light distribution

Throw light across your rooms in an even and uniform manner.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 142 mA
- Efficacy: 88 lm/W

## Power consumption

- Power factor: 0.5

## Product dimensions and weight

- Net weight: 0.42 kg
- Height: 5.8 cm
- Length: 32 cm
- Width: 32 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 320 mm
- Total lumen output fixture: 1500
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class I

**Packaging dimensions and weight**

- EAN/UPC - product: 6922341982286
- Net weight: 0.42 kg
- Gross weight: 0.64 kg
- Height: 35.4 cm
- Length: 6.4 cm
- Width: 35.4 cm



Issue date: 2025-02-17  
Version: 0.104

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)