

# PHILIPS

FC560 Ceiling Light  
24+15W

Ceiling Lights

6000/3000/4000K

White

SceneSwitch

6941970613156



## Comfortable LED light that's easy on your eyes

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

### Ambient light effect

- Ambience light mode

### Premium quality

- EyeComfort - light that's easy on the eyes

### Durability

- Long life span up to 15,000 hours

# Highlights

## Ambience light mode

Create a cozy, intimate atmosphere with the ambience light mode.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 95
- Color temperature: 2700-4000-6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 66 lm/W

## Miscellaneous

- Especially designed for: Bedroom
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: SceneSwitch

## Other characteristics

- Lamp current: 190 mA

#### Power consumption

- Power factor: 0.5

#### Product dimensions and weight

- Net weight: 4.6 kg
- Overall height: 260 mm

#### Packaging dimensions and weight

- Net weight: 4.6 kg
- Gross weight: 7.44 kg
- Height: 0
- Length: 0
- Width: 0

#### Service

- Warranty: 1 year(s)

#### Technical specifications

- Diameter: 410 mm
- Total lumen output fixture: 1300 @4000K
- Light color: 6000/3000/4000
- Mains power: AC 220
- Fixture dimmable: No
- IP code: IP20 | Finger-protected
- Class of protection: Class I - Earthed



Issue date: 2025-08-30  
Version: 0.66

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)