

PHILIPS

CL950 Ceiling Light
40W

Ceiling Lights

2700-6500K

White

SceneSwitch

6941970613323



Comfortable LED light that's easy on your eyes

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

High quality light

- EyeComfort – light that's easy on your eyes

Premium quality

- EyeComfort - light that's easy on the eyes

Eye Care

- 3D Backlight to restrains contrast glare

Highlights

EyeComfort – light that's easy on your eyes



Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour

rendition and dimming effects to ensure they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

3D Backlight

Apart from main light source, the additional Indirect light source from the backside to light up dim area of ceiling, reduces contrast of dim and bright for the space so that restrain contrast glare to provide comfort light

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 97
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: SceneSwitch

Other characteristics

- Lamp current: 210 mA
- Efficacy: 82 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 1.9 kg
- Height: 7 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 403 mm
- Total lumen output fixture: 3300
- Light color: 2700-6500
- Mains power: AC 220-240
- Fixture dimmable: Wireless Dim - Do not use with dimmer
- LED: Yes
- IP code: IP40
- Class of protection: Class II

Packaging dimensions and weight

- Net weight: 1.82 kg
- Gross weight: 2.32 kg
- Height: 0
- Length: 0
- Width: 0



Issue date: 2025-02-17
Version: 0.58

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com