

PHILIPS

CL950 Ceiling Light
140W Rectangular

Smart LED

Tunable white

IP40/Plastic/white

6941970613361



Smart lighting for you daily living

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

Smart control

- Voice control with Google Assistant, Alexa or Siri Shortcuts

Light modes

- Customize Scenes with preset dynamic light modes.
- Trigger different light modes

Highlights

Voice Control

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change color, and set custom light Scenes.

Customized Scenes

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WiZmote or voice.

Trigger different light modes

" By setting Rhythms for the room in the WiZ app, you can make your sensor trigger different light modes at different times of the day"

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Extra feature/accessory incl.

- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): >95
- Color temperature: 2700-6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 67 lm/W

Miscellaneous

- Especially designed for: Living Room, Kitchen, Dining Room, Bedroom
- EyeComfort: Yes

Other characteristics

- Lamp current: 710 mA

Power consumption

- Power factor: 0.9
- Voltage: 220-240 V

Product dimensions and weight

- Net weight: 9.5 kg
- Overall height: 90 mm
- Overall length: 965 mm
- Overall width: 652 mm

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 9500
- Light color: 2700-6500
- Wattage bulb included: 140
- IP code: IP40 | Wire-protected
- Class of protection: Class II – Double Insulated

What's supported

- Compatible with Effects: Yes
- WiFi: Wireless G
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Communication protocol: Bluetooth, WiFi (2.4GHz)

Packaging dimensions and weight

- Net weight: 8.7 kg
- Gross weight: 10.65 kg
- Height: 0
- Length: 0
- Width: 0



Issue date: 2025-09-17
Version: 0.65

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com