PHILIPS

CL400 Ceiling Light 24W

Ceiling Lights

5700K

White

6941970618533



Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes.

Light effect
- This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

Easy to experience
- Easy installation

Light effect
- Uniform light distribution

Premium quality
- Easy to clean

Durability
- Long life span up to 15,000 hours

Highlights

Interlaced Optics
This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

Easy installation
No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Uniform light distribution
Throw light across your rooms in an even and uniform manner.

Easy to clean
Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

Long life span up to 15,000 hours
Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics
- Intended use: Indoor

Design and finishing
- Color: White
- Material: Plastic

Durability
- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental
- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics
- Color consistency: 6 SDCM
- Color rendering index (CRI): 95
- Color temperature: 5700 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 83 lm/W

Miscellaneous
- Especially designed for: Bedroom
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics
- Lamp current: 205 mA

Power consumption
- Power factor: 0.5

Product dimensions and weight
- Net weight: 0.56 kg
- Overall height: 60 mm

Service
- Warranty: 1 year(s)

Technical specifications
- Diameter: 320 mm
- Total lumen output fixture: 2000
- Light color: 5700
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP40 | Wire-protected
- Class of protection: Class II - Double Insulated

Packaging dimensions and weight
- EAN/UPC - product: 6941970618533
- Net weight: 0.56 kg
- Gross weight: 0.97 kg
- Height: 36 cm
- Length: 8 cm
- Width: 35.5 cm

6941970618533



Issue date: 2025-08-30
Version: 0.97

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com