

# PHILIPS

Light Strip Light  
Strip 10m

Light Strips

3000K

White

Dimmable

6941970649261



## Durable and bright

LV strip offers bright and comfortable light

### Easy installation

- Cut to size

### Light effect

- Uniform light distribution

### Durability

- Long lasting quality, even after years

# Highlights

## Cut to size

Easily cut light strips to fit your spaces. Cut marks on the light strip indicate where to cut.

## Uniform light distribution

Throw light across your rooms in an even and uniform manner.

## Durable and long lasting

Made of robust materials selected for durability and visual appeal. Built for long-lasting performance. Install it and forget it until the end of its long useful life—no hassling with replacements. High-quality materials have UV baking, high temperature, and other endurance tests to ensure durability

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: No
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## String light/Lightstrip

- Extendibility: Yes

## Miscellaneous

- Especially designed for: Bedroom, Dining Room, Kitchen, Living Room
- Style: Contemporary
- Type: Light Strips
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 2920 mA

## Product dimensions and weight

- Net weight: 0.112 kg
- Height: 0.14 cm
- Length: 1,000 cm
- Width: 0.8 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 700
- Light color: 3000
- Mains power: DC 24
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class III – Safe Extra Low Voltage



Issue date: 2025-06-16  
Version: 0.89

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)