

PHILIPS

Fan Ceiling Light
33(fan)+36(ceiling)W

UltraEfficient

2700//6500K

White

6941970667586



Comfortable LED light that's easy on your eyes

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

High quality light

- EyeComfort – light that's easy on your eyes

Control

- Adjustable color temperature and brightness

Eye Care

- High quality of LED light brings out vivid colors

Highlights

EyeComfort – light that's easy on your eyes



Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever

to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade.

High quality LED light

Premium LED technology integrated into this Philips lamp. While instantly turned on, it enables an optimal light output and brings out vivid colors to assist kids' identification for color when drawing or reading

Adjustable color temperature and brightness

Changing color temperature and brightness allows you to change the mood and atmosphere in a room, matching the light to different kinds of activity.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 97
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Dining Room
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort, UltraEfficient

Other characteristics

- Lamp current: 370 mA
- Efficacy: 72 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 5.7 kg
- Height: 39 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Diameter: 435 mm
- Total lumen output fixture: 2600&4000K
- Light color: 2700-6500
- Mains power: AC 220-240
- Fixture dimmable: Yes
- IP code: IP40

- Class of protection: Class I - Earthed

Packaging dimensions and weight

- Net weight: 5.7 kg
- Gross weight: 5.7 kg
- Height: 0
- Length: 0
- Width: 0



Issue date: 2025-06-16
Version: 0.18

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com