

# PHILIPS

Linear fluorescent  
tube

TL-D Standard colours

36 W

G13

Cool daylight

871150070271540



## Bright and stylish home with slim design

Philips TL/TLDs Produce light efficiently, resulting in fewer replacements. They provide functional lighting that gives sufficient light levels for common areas.

### Gives you bright light

- Standard colors with moderate color rendering
- High initial light output

# Highlights

## Standard colors High initial light output

High Light output provides better light quality with more brightness and

allows more vibrance in home application.

# Specifications

## Bulb characteristics

- Socket: GU10
- Technology: Energy saving lamp
- Dimmable: Yes

## Durability

- Lumen maintenance factor: 0.9
- Nominal lifetime: 13,000

## Light characteristics

- Color rendering index (CRI): 72
- Color temperature: 6200 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 2500 lm
- Correlated Color Temperature (Nom): 6500 K
- Luminous Flux: 2,500 lm

## Power consumption

- Voltage: 230 V
- Power Consumption: 36.0
- Energy Consumption kWh/1000 h: 43

## Technical specifications

- Frequency: 50 Hz
- Shape: Linear
- Dimmable: Yes
- Cap-Base: G13 | Medium Bi-Pin  
Fluorescent

## Packaging dimensions and weight

- EAN/UPC - product: 8711500702715
- Net weight: 0.14 kg
- Gross weight: 0.17 kg
- Height: 2.7 cm
- Length: 121.5 cm
- Width: 2.7 cm



Issue date: 2025-06-13  
Version: 0.560

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)