

PHILIPS

Linear fluorescent
tube

TL-D Standard colours

36 W

G13

Cool daylight

871150070271540



Bright and stylish home with slim design

Philips TL/TLDs Produce light efficiently, resulting in fewer replacements. They provide functional lighting that gives sufficient light levels for common areas.

Gives you bright light

- Standard colors with moderate color rendering
- High initial light output

Highlights

Standard colors High initial light output

High Light output provides better light quality with more brightness and allows more vibrance in home application.

Specifications

Bulb characteristics

- Socket: GU10
- Technology: Energy saving lamp
- Dimmable: Yes

Durability

- Lumen maintenance factor: 0.9
- Nominal lifetime: 13,000 hour(s)

Light characteristics

- Color rendering index (CRI): 72
- Color temperature: 6200 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 2500 lm
- Correlated Color Temperature (Nom): 6500 K
- Luminous Flux: 2,500 lm

Power consumption

- Voltage: 230 V
- Wattage: 36 W
- Power Consumption: 36.0 W

Technical specifications

- Frequency: 50 Hz
- Shape: Linear
- Dimmable: Yes
- Cap-Base: G13 | Medium Bi-Pin
Fluorescent

Packaging dimensions and weight

- EAN/UPC - product: 8711500702715
- Net weight: 0.14 kg
- Gross weight: 0.17 kg
- Height: 2.7 cm
- Length: 121.5 cm
- Width: 2.7 cm



Issue date: 2025-04-19
Version: 0.560

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com