

PHILIPS

Spot 50W MR16
GU5.3

LED

3000K

390lm

15000h

8718699675653



Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

Choose for a sustainable solution

- Safe for any room and convenient to recycle

Highlights

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them

safe for any room and convenient to recycle.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Dimmable: No
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions

- Height: 4.6 cm
- Width: 5.1 cm

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +40 °C
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 60 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 390 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 390 lm
- Luminous Efficacy (rated) (Nom): 78 lm/W

Other characteristics

- Efficacy: 78 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699675653
- EOC: 871869967565300
- Product title: LEDspots 5-50W MR16 830 60D

Power

- Power Factor (Fraction): 0.6

Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Power Consumption: 5 W

Product dimensions and weight

- Length: 4.6 cm

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 400 cd

Technical specifications

- Frequency: 50 Hz
- Line Frequency: - Hz
- Dimmable: No
- Cap-Base: GU5.3

Packaging dimensions and weight

- EAN/UPC - product: 8718699675653
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 6 cm
- Length: 5.1 cm
- Width: 5.1 cm



Issue date: 2025-04-19
Version: 0.98

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com