

PHILIPS

Candle 15W T25 E14

LED

2700K

150lm

15000h



8718699771935



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- For use in refrigerators and freezers

Highlights

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect

sustainable replacement for traditional standard incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Special purpose appliance bulb

Philips refrigerator bulbs can be used in refrigerators, freezers, and similar places subject to low operating temperatures. Easily replace your appliance bulbs with a Philips refrigerator bulb for a long, useful life.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Guarantee

- Warranty period: 2 years

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 150 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 827 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 150 lm
- Stroboscopic effect visibility measure (SVM): 0.4
- Luminous Efficacy (rated) (Nom): 88.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699771935
- EOC: 871869977193501
- Product title: LED 15W T25 E14 WW FR ND RF 1SRT6

Power

- Power Factor (Fraction): 0.4

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage equivalent: 15 W
- Energy Efficiency Label (EEL): F
- Power Consumption: 1.7 W
- Energy Consumption kWh/1000 h: 2

Product dimensions and weight

- Overall height: 59 mm
- Overall length: 59 mm
- Overall width: 25 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Diameter: 25 mm
- EPREL Registration Number: 391879
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM) – Flickering value as per EN 61000-3-3: 1
- Line Frequency: 50 to 60
- Cap-Base: E14
- can it be used in closed luminaires: No

Packaging dimensions and weight

- EAN/UPC – product: 8718699771935
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm



Issue date: 2025-09-13
Version: 0.539

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com