

PHILIPS

Bulb 80W T60 E27

LED

3000K

1200lm

15000h

8719514252813



Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

High quality LED light that lasts for decades

- Switch to extra brightness

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

EyeComfort with concaved optical design

This bulb brings a comfortable, energy-efficient and long-lasting lamp with a concave design that casts a wide beam for extra brightness.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: T60
- Socket: E27
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Bulb dimensions

- Height: 11.05 cm
- Width: 6 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 109 lm/W

Packaging information

- EAN: 8719514252813
- EOC: 871951425281300
- Product title: LEDBright 11W E27 3000K 230V 1CT/12 APR

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 11 W
- Wattage equivalent: 80 W

Product dimensions and weight

- Length: 11.05 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8719514252813
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 11.9 cm
- Length: 6.3 cm
- Width: 6.3 cm
- Material number (12NC): 929002433007



Issue date: 2024-03-29
Version: 0.159

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com