

# PHILIPS

Garnet Ceiling Light  
40W

Ceiling Lights

4000K

White



8720169195295



## One fixture. Your switch. Three light settings.

Changing the ambiance in your room has never been easier. Philips' SceneSwitch LED ceiling light lets you set the mood with three unique settings. The combination of main and indirect light give you options that are perfect for your get together, concentrate and cozy moments. No dimmer or installation required - all you need is your existing switch

### Easy to experience

- Easy installation

### Light effect

- Indirect light
- Triple-zone light
- Soft harmonious light

### Premium quality

- EyeComfort - light that's easy on the eyes

# Highlights

## Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

## Indirect light

Volcano lamp shade decorates your space and softly reflects light.

## Triple-zone light

Triple-zone light source gives you the flexibility to create the ambiance you want.

## Soft harmonious light

The right combination of indirect and direct light diffuses a warm glow throughout your space with no glare.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 200 mA
- Efficacy: 110 lm/W

## Power consumption

- Power factor: 0.9

## Product dimensions and weight

- Net weight: 1.23 kg
- Height: 9.9 cm
- Length: 50 cm
- Width: 50 cm

## Service

- Warranty: 5 year(s)

#### Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 500 mm
- Total lumen output fixture: 4400
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 40
- IP code: IP20
- Class of protection: Class II

#### Packaging dimensions and weight

- EAN/UPC - product: 8720169195295
- Net weight: 1.3 kg
- Gross weight: 3.16 kg
- Height: 54 cm
- Length: 13 cm
- Width: 54 cm
- Material number (12NC):  
929003316301



Issue date: 2024-09-06  
Version: 0.384

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)