

# PHILIPS

## PC Screen Light

myHomeOffice

66219 Edison Pro

PC screen light

929003602301



# Comfortable LED light that's easy on your eyes

High CRI and vivid light quality. Asymmetric optics. Liner tunable color temperature. Integrated motion sensor.

### Easy on your eyes

- Scientific light distribution

### Control

- Multi-level step dimming

### Control

- Tunable color temperature

# Highlights

**Scientific light distribution****Multi-level step dimming**

Intuitive multi-level brightness control setting gives you great control over

your lights and to create the light ambiance that you need.

**Tunable color temperature**

Shift from crisp white light for focus to a warm yellow light for relaxation.

# Specifications

**Bulb characteristics**

- Intended use: Indoor

**Design and finishing**

- Color: Black
- Material: Metal, Plastic

**Extra feature/accessory incl.**

- LED integrated: Yes

**Light characteristics**

- Color rendering index (CRI): 90

**Miscellaneous**

- Especially designed for: Home office & Study
- EyeComfort: Yes

**Service**

- Warranty: 1 year(s)

**Technical specifications**

- IP code: IP20

**Packaging dimensions and weight**

- EAN/UPC – product: 8720169179943
- Net weight: 0.41 kg
- Gross weight: 0.67 kg
- Height: 66 mm
- Length: 484 mm
- Width: 115 mm



Issue date: 2025-04-25  
Version: 0.123

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)