



Bring imagination to light

Flexible LED strips can be curved around corners, trimmed and connected to any required length. Take your creativity off the straight and narrow, and experiment in exploring new ways to use the LED strip!

Ease of use

· Smooth surface finish for easy cleaning

Long lifespan

• Extremely long life 20,000 hours

Energy saving

• Built-in LED, as part of the system

Highlights

Easy to maintain



Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Specifications

Bulb characteristics

· Intended use: Indoor

Design and finishing

Color: TransparentMaterial: Plastic

Durability

• Number of switch cycles: 10,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: No
- Dimmable with remote control: No
- · LED integrated: Yes
- · On/off switch on wire: No
- · Power adapter included: Yes
- · Remote control included: No

Light characteristics

- · Color consistency: 5 SDCM
- · Color rendering index (CRI): 80

String light/Lightstrip

· Extendibility: No

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway
- Style: Contemporary
- Type: Light Strips
- · EyeComfort: No

Other characteristics

- Lamp current: 160 mA
- Efficacy: 81 lm/W

Product dimensions and weight

- · Net weight: 0.265 kg
- · Height: 0.2 cm
- · Length: 500 cm
- · Width: 0.8 cm

Service

Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 325
- · Light color: 3000
- Mains power: AC 220-240
- · Fixture dimmable: No
- · LED: Yes
- Wattage bulb included: 4(20)
- Maximum wattage replacement bulb:
 - 18 W
- IP code: IP20
- · Class of protection: Class II
- · Number of light sources: 1



Issue date: 2025-04-19 Version: 0.714 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.