



# State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

## Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

## Highlights

#### No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won $\phi_{\P}$ t fade.

### **Contains no mercury**



No mercury allows for non-hazardous waste disposal, so this characteristic provides a simple way to make your current space more sustainable.

# **Specifications**

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non directional bulb

· Socket: E27

Bulb Finish: FrostedDimmable: No

· Bulb Material: Plastic

#### **Durability**

Number of switch cycles: 50,000Nominal lifetime: 8,000

### Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### **Light characteristics**

• Beam angle: 150 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 6500 K

· Nominal luminous flux: 720 lm

 Warm-up time to 60% light: instant full light

· Color Code: 865 | CCT of 6500K

 Luminous Efficacy (rated) (Nom): 102 lm/W

### Miscellaneous

EyeComfort: No

#### **Packaging information**

EAN: 8719514286405EOC: 871951428640500

• Product title: ESS LEDBulb 7W E27

6500K 230V 4CT/3 ID

#### **Power consumption**

• Power factor: 0.5

· Voltage: 220-240 V

· Wattage equivalent: 65 W

• Power Consumption: 7 W

#### Product dimensions and weight

Overall height: 108 mmOverall length: 108 mmOverall width: 60 mm

#### **Rated values**

· Rated peak intensity: 156 cd

#### **Technical specifications**

• Frequency: 50-60

#### Packaging dimensions and weight

• EAN/UPC - product: 8719514286405

Net weight: 0.28 kgGross weight: 0.34 kg

Height: 11.9 cmLength: 6.2 cmWidth: 24.9 cm



Issue date: 2025-08-30 Version: 0.55 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips