



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light wonφηt fade.

Contains no mercury



No mercury allows for non-hazardous waste disposal, so this characteristic provides a simple way to make your current space more sustainable.

Specifications

Bulb characteristics

Intended use: Indoor

· Lamp shape: Non directional bulb

· Socket: E27

 Bulb Finish: Frosted · Dimmable: No Bulb Material: Plastic

Durability

• Number of switch cycles: 50,000 · Nominal lifetime: 12.000

Environmental

· Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Beam angle: 150 degree(s) · Color rendering index (CRI): 80 · Color temperature: 6500 K

· Nominal luminous flux: 950 lm

• Warm-up time to 60% light: instant

full light

· Color Code: 865 | CCT of 6500K · Luminous Efficacy (rated) (Nom): 105 lm/W

Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

Packaging information

• EAN: 8719514468849 • EOC: 871951446884900

· Product title: LEDBulb 9W E27 6500K

230V 4CT/3 IDOL

Power consumption

· Power factor: 0.5 · Voltage: 220-240 V

· Wattage equivalent: 80 W • Power Consumption: 9 W

Product dimensions and weight

· Overall height: 108 mm · Overall length: 108 mm · Overall width: 60 mm

Rated values

· Rated peak intensity: 190 cd

Technical specifications

• Frequency: 50-60

Packaging dimensions and weight

• EAN/UPC - product: 8719514468849

· Net weight: 0.14 kg · Gross weight: 0.2 kg · Height: 11.9 cm · Length: 6.2 cm

· Width: 24.9 cm



Issue date: 2025-08-30 Version: 0.72

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips