

# PHILIPS

Filament Bulb  
Frosted 75W A60 E27

UltraEfficient

6500K

1000lm

50000h

8720169238121



## Bright LED lighting with excellent light quality

LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Saves up to 90% Energy
- Long life bulb - Lasts up to 50 years

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

## Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1000 lm
- Warm-up time to 60% light: instant full light
- Color Code: 865 | CCT of 6500K
- Luminous Efficacy (rated) (Nom): 200 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: UltraEfficient, EyeComfort

## Packaging information

- EAN: 8720169238121
- EOC: 872016923812100
- Product title: LED CLA A60 5W E27 6500K FR UE1CT/12

## Power consumption

- Power factor: 0.4
- Voltage: AC 220-240 V
- Wattage equivalent: 75 W
- Power Consumption: 5 W

#### Product dimensions and weight

- Overall height: 104 mm
- Overall length: 104 mm
- Overall width: 60 mm

#### Technical specifications

- Frequency: 50-60

#### Packaging dimensions and weight

- EAN/UPC – product: 8720169238121
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 12 cm
- Length: 6.6 cm
- Width: 6.6 cm



Issue date: 2025-08-30  
Version: 0.175

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)