



# Frosted LED candle bulbs for decorative fixtures

Philips LED frosted candles provide a soft, diffuse light effect and an exceptionally long life. With a pure and elegant design, this light bulb is the perfect match for chandelier fixtures with small (E27) fittings.

# High quality light

· No visible flicker

### Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

# Create the right light for your home

Perfect for decorative fixtures

# Highlights

#### No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

# 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

#### Perfect for decorative fixture



Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips, and post lights.

# **Specifications**

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non directional candle

· Socket: E27

Bulb Finish: FrostedDimmable: No

· Bulb Material: Plastic

# **Durability**

• Number of switch cycles: 50,000

· Nominal lifetime: 15,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## **Light characteristics**

· Color rendering index (CRI): 80

· Color temperature: 2700 K

Nominal luminous flux: 620 lm

 Luminous Efficacy (rated) (Nom): 103 lm/W

#### Miscellaneous

• EyeComfort: No

# **Packaging information**

• EAN: 8720169336377

• EOC: 872016933637700

 Product title: ESSLEDCandle 6W E27 2700K 1PF/12 ID

# **Power consumption**

• Power factor: 0.51

Voltage: AC 220-240 VWattage equivalent: 61 WPower Consumption: 6 W

### Product dimensions and weight

Overall height: 104 mmOverall length: 104 mmOverall width: 35 mm

# **Technical specifications**

• Frequency: 50-60

#### Packaging dimensions and weight

• EAN/UPC - product: 8720169336377

Net weight: 0.02 kgGross weight: 0.03 kg

Height: 14.1 cmLength: 3.6 cmWidth: 3.6 cm



Issue date: 2025-08-30 Version: 0.206 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips