

# PHILIPS

## Becken Recessed Recessed Light

Recessed Lights

4000K

White

8720169355828



## Superior light and style

Deep recessed for visual comfort

### Match your interior

- Expressive and elegant form

### Light effect

- Bright light with uniform distribution

### Safety

- LED protective cover for optimal light source insulation and ensure safety

### Premium quality

- EyeComfort - light that's easy on the eyes

# Highlights

## Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## LED protective cover for optimal light source insulation and ensure safety

Protects the LED itself to ensure it is protected when travelling and installing.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a

decade. Switch to light that's easy on your eyes. Your eyes will thank you.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal

## Durability

- Number of switch cycles: 12,500
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 90
- Color temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 71 lm/W

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Lamp current: 62 mA

## Power consumption

- Power factor: 0.5
- Power Consumption: 7

## Product dimensions and weight

- Net weight: 0.14 kg
- Recessed distance: 250 mm
- Overall height: 50 mm

### Service

- Warranty: 3 year(s)

### Technical specifications

- Diameter: 85 mm
- Total lumen output fixture: 500
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

### Packaging dimensions and weight

- EAN/UPC – product: 8720169355828
- Net weight: 0.14 kg
- Gross weight: 0.18 kg
- Height: 8.5 cm
- Length: 10.5 cm
- Width: 10.5 cm



Issue date: 2025-08-02  
Version: 0.81

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)