



Superior light and style

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Match your interior

· Expressive and elegant form

Light effect

· Bright light with uniform distribution

Premium quality

• EyeComfort - light that's easy on the eyes

Highlights

Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip

s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Bulb characteristics

· Intended use: Indoor

Design and finishing

· Color: White

Material: Metal. Plastic

Durability

Number of switch cycles: 30,000

• Nominal lifetime: 30,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

Light characteristics

• Beam angle: 110 degree(s)

- · Color consistency: 5 SDCM
- · Color rendering index (CRI): 80
- · Color temperature: 6500 K
- · Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- · LED Innovations: EyeComfort

Other characteristics

· Lamp current: 27 mA

Power consumption

- Power factor: 0.9
- Power Consumption: 6

Product dimensions and weight

- Net weight: 0.125 kg
- Recessed distance: 50 mm
- Overall height: 40 mm
- · Overall length: 130 mm
- · Overall width: 130 mm
- Recessed Ceiling cutout: 10.0 cm x 10.0 cm

Service

Warranty: 3 year(s)

Technical specifications

· Diameter: 125 mm

• Total lumen output fixture: 600

· Light color: 6500

Mains power: AC 220-240Fixture dimmable: No

IP code: IP20 | Finger-protectedClass of protection: Class II - Double

Insulated

• Number of light sources: 1

Packaging dimensions and weight

• EAN/UPC - product: 8720169363007

Net weight: 0.13 kgGross weight: 0.22 kgHeight: 13.4 cmLength: 17.2 cm

• Width: 13.2 cm



Issue date: 2025-09-03 Version: 0.41

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.