

PHILIPS

Meson Recessed Light

Recessed Lights

6500K

White

8721103042293



Designed for your dream home

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Light effect

- Bright light with uniform distribution

Premium quality

- EyeComfort - light that's easy on the eyes

Durability

- Long life span up to 25,000 hours

Highlights

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 12,500
- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 90 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Home Office, Hotel & Restaurant, Kitchen, Living Room
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Lamp current: 144 mA
- Efficacy: 70 lm/W

Power consumption

- Power factor: 0.5
- Power Consumption: 17

Product dimensions and weight

- Net weight: 0.111 kg
- Height: 5 cm
- Recessed distance: 50 mm

Packaging dimensions and weight

- EAN/UPC – product: 8721103042316
- Net weight: 0.11 kg
- Gross weight: 0.17 kg
- Height: 17.2 cm
- Length: 5.3 cm
- Width: 17 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Diameter: 165 mm
- Total lumen output fixture: 1200
- Light color: 3000
- Mains power: AC 220–240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class II – Double Insulated
- Number of light sources: 1



Issue date: 2025-06-14
Version: 0.152

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com