



# Durable LED task lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. This Philips LED tube is perfect for the places that need a lot of light.

#### Choose for a sustainable solution

• Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 50% in energy by replacing your existing fluorescent tubes (banned by EU regulation since 2023).

### High quality LED light that lasts for decades

 With a lifetime of 15,000 hours, you can reduce the hassle of frequently replacing your light sources and enjoy a perfect lighting solution for over 15 years.

#### Choose a simple replacement for your old fluorescents

 The perfect replacement for linear fluorescent tubes that fits straight into existing luminaires. Simply plug and play without any hassle for rewiring.

# Highlights

Saves over 50% energy compared to fluorescents

Long lasting for 15,000 hours Fast and easy to install

# Specifications

#### **Bulb characteristics**

Intended use: IndoorLamp shape: T8Socket: G13

Bulb Finish: FrostedDimmable: NoBulb Material: Glass

#### **Durability**

Number of switch cycles: 50,000

· Nominal lifetime: 15,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### **Light characteristics**

Beam angle: 240 degree(s)Color rendering index (CRI): 80

Color temperature: 4000 KNominal luminous flux: 2700 lm

 Luminous Efficacy (rated) (Nom): 108 lm/W

#### Miscellaneous

· EyeComfort: Yes

· LED Innovations: EyeComfort

# Packaging information

EAN: 8721103047366EOC: 872110304736600

• Product title: LEDtube HO+ 1200mm

25W 840 T8 AP C G ID

## **Power consumption**

• Power factor: 0.5

Voltage: AC 220-240 VWattage equivalent: 36 WPower Consumption: 25 W

#### Product dimensions and weight

Overall height: 1,213 mmOverall length: 1,213 mmOverall width: 28 mm

## **Technical specifications**

• Frequency: 50-60

#### Packaging dimensions and weight

• EAN/UPC - product: 8721103047366

Net weight: 0.17 kgGross weight: 0.22 kgHeight: 3 cm

Height: 3 cmLength: 125.2 cmWidth: 3 cm



Issue date: 2025-10-04 Version: 0.178 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips