

PHILIPS

Halogen linear lamp

1500 W

R7s cap

Clear

8727900808575



Superior halogen lighting

Provides bright, sparkling light with superior dimmability. With its high light output, it's perfect for floodlighting gardens, terraces and other outdoor areas at night.

Personal scene setting

- Best dimmiability to dims and create a cosy atmopshere

Create a cosy atmosphere

- Bright halogen light provides better contrast for more focus
- Bright, sparking lighting to create your light scene at home

Floodlighting

- Maximum light output to create floodlighting

Highlights

Best dimmability

This lamp can be used in combination with all dimmers and will not only turn down the light to 0% but also create a cosy atmosphere as you are used to with your incandescent.

Halogen contrast for focus

With bright halogen light, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes for a better focus.

Bright, sparkling light

Clear halogen is a sparkling light, giving beautiful reflections where it shines, and sharp shadows where it doesn't. Philips halogen lamps give decorative light effect to your room, to bring your room to life.

Maximum light output

Maximum light output to create floodlighting.

Specifications

Bulb characteristics

- Shape: Linear
- Socket: R7s
- Bulb Finish: Clear
- Dimmable: Yes

Bulb dimensions

- Height: 12 mm
- Width: 254.1 mm

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Number of switch cycles: 8,000
- Nominal lifetime: 2,000 hour(s)

Light characteristics

- Application: Special application
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Light Color Category: Clear
- Nominal luminous flux: 33000 lm
- Warm-up time to 60% light: instant full light s
- Correlated Color Temperature (Nom): 2900 K
- Luminous Flux: 33,000 lm
- Luminous Efficacy (rated) (Nom): 22 lm/W

Power

- Power Factor (Fraction): 1

Power consumption

- Voltage: 230 V
- Wattage: 1,500 W
- Power Consumption: 1,500.0 W

Rated values

- Rated lifetime: 2,000 hour(s)

Technical specifications

- Dimmable: Yes
- Cap-Base: R7s

Packaging dimensions and weight

- EAN/UPC – product: 8727900808575
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 26 cm
- Length: 2.1 cm
- Width: 2.1 cm
- Material number (12NC): 923932243241



Issue date: 2024-04-02
Version: 0.469

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com