





Enjoy a beautiful garden with light

The Philips myGarden Raccoon wall light in structured anthracite grey lights up outdoor areas powerfully for whatever you like. LED lights, synthetic materials and minimalist design give a contemporary feel to your outdoor space.

Sustainable light solutions

- Energy saving
- High quality LED light
- · Long operating life of up to 15 years
- $\bullet \ \text{Warm white light} \\$
- $\boldsymbol{\cdot}$ Philips offers a 5-year warranty on the LED module and driver

Designed for your garden

· IP44 - weatherproof

Highlights

Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Long operating life



A light source you can trust. The integrated LEDs used in this Philips LED lamp will last up to 15,000 hours (which equals 15 years on the basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

Warm white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

IP44 - weatherproof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

Specifications

Design and finishing

Colour: AnthraciteMaterial: Metal

Durability

· Nominal lifetime: 25,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

Fully weatherproof: YesLED integrated: Yes

Garden area

· Garden area: Garden and Patio

Light characteristics

· Colour temperature: 2700 K

Miscellaneous

• Especially designed for: Garden, Patio

Style: ContemporaryType: Wall LightsEyeComfort: Yes

• Extra Features: Water Resistant

Product dimensions and weight

Net weight: 0.620 kg
Overall height: 205 mm
Overall length: 162 mm
Overall width: 66 mm

Service

· Warranty: 2 year(s)

Technical specifications

 Light source equivalent to traditional bulb of: 30

· Total lumen output fixture: 400 lm

Bulb technology: LEDLight colour: warm whiteMains power: 50-60 Hz

• Energy class included light source: F

· Wattage bulb included: 4 W

 IP code: IP44 | Wire-protected and splash-proof

 Class of protection: Class II – Double Insulated

Light source replaceable: NoNumber of light sources: 1

Packaging dimensions and weight

• EAN/UPC - product: 8718291479468

Gross weight: 0.68 kgHeight: 22.8 cmLength: 7.8 cmWidth: 16.3 cm

· Net weight: 0.62 kg



Issue date: 2025-09-13 Version: 0.490 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips