

PHILIPS

Spot 50 W PAR16
GU10 x6

LED

4000K

390 lm

15000 h

Non-dimmable



8718696764657



Experience Cool White LED Light

This Philips LED spot provides a dimmable, focused bright beam, an exceptionally long life and significant energy savings. This spot is the perfect long-lasting replacement for 50 W spots with a GU10 cap.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Saves up to 80% energy

High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Saves up to 80% energy



Enjoy the energy savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Shape: Spot
- Lamp shape: Directional reflector
- Socket: GU10
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 390 lm
- Warm-up time to 60% light: 0.5
- Luminous efficacy (rated) (nom.): 72 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Packaging information

- Product family: EyeComfort

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage equivalent: 50 W
- Energy efficiency label (EEL): F
- Power Consumption: 4.6 W
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 391859

Rated values

- Rated peak intensity: 770 cd



Issue date: 2025-08-27
Version: 0.978

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com