



Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 85% less energy than traditional light bulbs thanks to the latest LED energy-saving technology, and last ten times longer.

Choose a simple replacement for your old lamps

· Similar shape and size as standard incandescent bulbs

Create the right light for your home

· Perfect for general room lighting

High-quality LED light that lasts for decades

• Designed for the comfort of your eyes

Highlights

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non-directional candle

Socket: B15Dimmable: NoLamp Finish: ClearBulb material: Glass

Durability

• Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

· Colour rendering index (CRI): 80

• Colour temperature: 2700 K

Nominal luminous flux: 470 lm

Warm-up time to 60% light: 0.5Colour Code: 827 | CCT of 2700K

· Luminous efficacy (rated) (nom.): 109

lm/W

Miscellaneous

EveComfort: Yes

· LED innovations: EyeComfort

Packaging information

• EAN: 8718699763091

• EOC: 871869976309100

 Product title: LED classic 40W B35 B15 WW CL ND SRT4

Power consumption

• Power factor: 0.41

· Voltage: 220-240 V

· Wattage equivalent: 40 W

· Energy efficiency label (EEL): F

• Power Consumption: 4.3 W

Energy consumption kWh/1,000

hours: 5

Product dimensions and weight

· Overall height: 97 mm · Overall length: 97 mm • Overall width: 35 mm

Technical specifications

• Frequency: 50-60

• EPREL Registration Number: 387403

Packaging dimensions and weight

• EAN/UPC - product: 8718699763091

· Net weight: 0.01 kg · Gross weight: 0.03 kg · Height: 14.6 cm

· Length: 4.6 cm





Issue date: 2025-08-30 Version: 0.156

@ 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips