



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

Choose a simple replacement for your old lamps

• Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

· Long-life bulbs – Last up to 15 years

Light beyond illumination

• For use in fridges and freezers

Highlights

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect

sustainable replacement for traditional standard incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Special-purpose appliance bulb

Philips fridge bulbs can be used in fridges, freezers and similar places subject to low operating temperatures. Easily replace your appliance bulbs with a Philips fridge bulb for a long, useful life.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non-directional lustre

Socket: E14Dimmable: NoLamp Finish: FrostedBulb material: Plastic

Durability

• Number of switch cycles: 50,000

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Guarantee

· Warranty period: 2 years

Light characteristics

- Beam angle: 240 degree(s)
- · Colour rendering index (CRI): 80
- · Colour temperature: 2700 K
- · Nominal luminous flux: 150 lm
- Warm-up time to 60% light: 0.5 s
- · Colour Code: 827 | CCT of 2700K
- Correlated Colour Temperature (Nom): 2700 K
- Luminous Flux: 150 lm
- · Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 88.00 lm/W

Miscellaneous

- EveComfort: Yes
- LED innovations: EyeComfort

Other characteristics

• EU RoHS compliant: Yes

Packaging information

- EAN: 8718699771935
- EOC: 871869977193502
- Product title: LED 15W T25 E14 WW FR ND RF 1SRT6 UK

Power

• Power Factor (Fraction): 0.4

Power consumption

Power factor: 0.4Voltage: 220-240 V

• Wattage equivalent: 15 W

Energy efficiency label (EEL): FPower Consumption: 1.7 W

• Energy consumption kWh/1,000

hours: 2

Product dimensions and weight

Overall height: 59 mmOverall length: 59 mmOverall width: 25 mm

Rated values

· Rated lifetime: 15,000

Technical specifications

Frequency: 50-60Diameter: 25 mm

• EPREL Registration Number: 391879

· Dimmable: No

Flickering value (PstLM): 1Line Frequency: 50 to 60

· Cap base: E14

Can it be used in closed luminaires:

Issue date: 2025-09-13

Version: 0.539

No

Packaging dimensions and weight [LED 15W T25 E14 WW FR ND RF 1SRT6 UK1

• EAN/UPC - product: 8718699771935

Net weight: 0.01 kgGross weight: 0.02 kgHeight: 12.7 cm

Length: 2.5 cmWidth: 6.3 cm

Packaging dimensions and weight [LED 15W T25 E14 WW FR ND RF 1SRT6]

• EAN/UPC - product: 8718699771935

Net weight: 0.01 kgGross weight: 0.02 kgHeight: 12.7 cm

Length: 2.5 cmWidth: 6.3 cm



© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips