

# PHILIPS

Spot 35 W PAR16  
GU10

LED

2700K

255 lm

15000 h



8718699774158



## Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

### High-quality light

- True incandescent-like warm white light

# Highlights

## True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Lamp dimensions

- Height: 5.4 cm
- Width: 5 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 255 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- Efficacy: 72 lm/W

## Packaging information

- EAN: 8718699774158
- EOC: 871869977415800
- Product title: LED classic 35W GU10 WW 36D RF ND SRT4

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage equivalent: 35 W
- Energy efficiency label (EEL): F
- Power Consumption: 3.5 W
- Energy consumption kWh/1,000 hours: 4

## Product dimensions and weight

- Length: 5.4 cm

## Rated values

- Rated peak intensity: 545 cd

## Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 391855

**Packaging dimensions and weight**

- EAN/UPC – product: 8718699774158
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-06-13  
Version: 0.248

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)