









# Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 85% less energy than traditional light bulbs thanks to the latest LED energy-saving technology, and last ten times longer.

#### Choose a simple replacement for your old lamps

· Similar shape and size as standard incandescent bulbs

### Create the right light for your home

Perfect for general room lighting

# High-quality LED light that lasts for decades

· Designed for the comfort of your eyes

# Highlights

#### Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

# Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

# Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non-directional bulb

· Socket: E27

Lamp Finish: ClearDimmable: No

· Bulb material: Glass

#### **Durability**

· Number of switch cycles: 20,000

· Nominal lifetime: 15,000

#### **Environmental**

• Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

#### **Light characteristics**

· Colour rendering index (CRI): 80

· Colour temperature: 2700 K

· Nominal luminous flux: 806 lm

· Warm-up time to 60% light: 0.4

· Colour Code: 827 | CCT of 2700K

 Luminous efficacy (rated) (nom.): 115 lm/W

#### Miscellaneous

EveComfort: Yes

· LED innovations: EyeComfort

#### **Packaging information**

• EAN: 8718699777579

• EOC: 871869977757900

 Product title: LED classic 60W A60 E27 WW CL ND RFSRT4

#### **Power consumption**

• Power factor: 0.51

· Voltage: 220-240 V

· Wattage equivalent: 60 W

· Energy efficiency label (EEL): E

• Power Consumption: 7 W

Energy consumption kWh/1,000

hours: 7

# Product dimensions and weight

Overall height: 106 mmOverall length: 106 mmOverall width: 60 mm

# **Technical specifications**

• Frequency: 50-60

• EPREL Registration Number: 1825152

# Packaging dimensions and weight

• EAN/UPC - product: 8718699777579

Net weight: 0.06 kg
Gross weight: 0.1 kg
Height: 14.6 cm
Length: 6.5 cm
Width: 6.3 cm



Issue date: 2025-09-24 Version: 0.367 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V