

PHILIPS

Lamp (Dimmable)

LED

6.5W-20W

E27

Flame

Dimming



8719514315396



State-of-the-art LED for the home

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

Dimmable extra warm white light


- Dimmable extra warm white light

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Dimmable extra warm white light



Offering cosy and warm ambiance in your room with extra warm white lights, which can dim to create your private atmosphere.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Dimmable: Yes
- Lamp Finish: smoky
- Bulb material: Glass

Lamp dimensions

- Height: 28.6 cm
- Width: 20.2 cm

Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 1800 K
- Nominal luminous flux: 200 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 818 | CCT of 1800K
- Correlated Colour Temperature (Nom): 1800 K
- Luminous Flux: 200 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 30 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Decorative

Other characteristics

- Efficacy: 30 lm/W
- CE mark: Yes
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514315396
- EOC: 871951431539600
- Product title: LED giant 20W E27 G200 1800K smoky D

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage equivalent: 20 W
- Power Consumption: 6.5 W
- Energy consumption kWh/1,000 hours: 7

Product dimensions and weight

- Length: 28.6 cm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60 Hz
- Diameter: 202 mm
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60 Hz
- Dimmable: Only with specific dimmers
- Cap base: E27



Issue date: 2025-06-13
Version: 0.349

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com