





Dimming



# Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

# Choose for a sustainable solution

· Saves up to 90% Energy

## Create the right light for your home

· Perfect for general room lighting

# Highlights

# Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

# Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

# Specifications

### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non-directional bulb

Socket: E27

· Lamp Finish: Clear

· Dimmable: Yes

· Bulb material: Glass

#### **Durability**

• Number of switch cycles: 20,000

· Nominal lifetime: 15,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

#### **Light characteristics**

· Colour rendering index (CRI): 90

· Colour temperature: 2200-2700 K

· Nominal luminous flux: 806 lm

· Warm-up time to 60% light: 0.5

 Colour Code: 922-927 | CCT of 2200K-2700K

 Luminous efficacy (rated) (nom.): 136 lm/W

#### Miscellaneous

EveComfort: Yes

· LED innovations: EyeComfort

• Extra Features: Dimmable,

WarmGlow

#### **Packaging information**

• EAN: 8719514323834

• EOC: 871951432383401

• Product title: LED classic 60W A60

E27 CL WGD90 SRT4 UK

#### **Power consumption**

• Power factor: 0.6

· Voltage: 220-240 V

· Wattage equivalent: 60 W

· Energy efficiency label (EEL): D

• Power Consumption: 5.9 W

• Energy consumption kWh/1,000

hours: 6

#### Product dimensions and weight

· Overall height: 104 mm

· Overall length: 104 mm

· Overall width: 60 mm

## **Technical specifications**

• Frequency: 50-60

• EPREL Registration Number: 1109131

# Packaging dimensions and weight

• EAN/UPC - product: 8719514323834

Net weight: 0.03 kgGross weight: 0.05 kg

Height: 14.6 cmLength: 6.5 cmWidth: 6.3 cm



Issue date: 2025-09-13 Version: 0.443 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V