

# PHILIPS

Bulb 100 W A60 B22

LED

2700K

1521 lm

15000 h



8720169326057



## Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High-quality light

- Designed for the comfort of your eyes

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: B22
- Dimmable: No
- Lamp Finish: Frosted
- Bulb material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 150 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 1521 lm
- Luminous efficacy (rated) (nom.): 117 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- EAN: 8720169326057
- EOC: 872016932605700
- Product title: LED 100W A60 B22 WW FR ND 1SRT4

## Power consumption

- Power factor: 0.6
- Voltage: AC 220-240 V
- Wattage equivalent: 100 W
- Power Consumption: 13 W
- Energy consumption kWh/1,000 hours: 13

#### Product dimensions and weight

- Overall height: 118 mm
- Overall length: 118 mm
- Overall width: 60 mm

#### Technical specifications

- Frequency: 50-60

#### Packaging dimensions and weight

- EAN/UPC – product: 8720169326057
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 15.6 cm
- Length: 6.6 cm
- Width: 6.4 cm



Issue date: 2025-08-02  
Version: 0.200

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)