

# PHILIPS

Kiskadee Wall Light  
42W E27 No-bulb

myGarden

No bulb

Antracite

Water Resistant



17383/93/PN



## Enjoy a beautiful garden with light

This elegant Philips anthracite wall light has clean lines and strong accents. It's made from high quality aluminum and it looks great in a contemporary garden. All you have to do is switch on the light and enjoy your garden.

### Designed for outdoors

- High quality aluminum and superior synthetics

### Special characteristics

- Weather proof

### Enjoy your outdoor life

- Create a stylish and welcoming atmosphere

# Highlights

## High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminum and superior synthetics.

## Create a stylish atmosphere

This outdoor wall light is designed around the latest trends and lifestyles to blend effortlessly into your outdoor space and define the ambiance you have always desired.

## Weather proof



This Philips outdoor lamp is especially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

# Specifications

## Design and finishing

- Color: Anthracite
- Material: Metal

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: No

## Garden area

- Garden area: Garden & Patio

## Light characteristics

- Luminous Efficacy (rated) (Nom): 121 lm/W

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

**Product dimensions and weight**

- Net weight: 0.545 kg
- Overall height: 212 mm
- Overall length: 197 mm
- Overall width: 140 mm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Mains power: 50-60 Hz
- Energy class included light source: no bulb included
- Fitting/cap: E27
- Wattage bulb included: -
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II - Double Insulated
- Light source replaceable: Yes
- Number of light sources: 1

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696165850
- Net weight: 0.55 kg
- Gross weight: 0.7 kg
- Height: 22.4 cm
- Length: 14.6 cm
- Width: 20.1 cm



Issue date: 2026-01-31  
Version: 0.554

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)