

# PHILIPS

## Downlight

Functional

PowerGlow

White

8.5W



8710619962638



## Durable and bright

Philips PowerGlow downlights provides brightest efficacy of 120Lm/watt suitable for commercial spaces also, recessed diffuser helps in glare reduction

### Match your interior

- Expressive and elegant form

### Light effect

- Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

### Material & finishing

- Durable aluminum housing

### Durability

- Long life LED light source
- Long life span up to 30,000 hours
- Energy saving

# Highlights

## Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

## Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

## Long life LED light source

Provides you with a long term lighting investment which offers equal quality light years down the line.

## Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

## Energy saving

Saves energy - which is good for your bills, and the environment.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Color: White
- Material: Metal

## Durability

- Lumen maintenance factor: 70%
- Nominal lifetime: 35,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 120 lm/W

## Miscellaneous

- Especially designed for: Living Room

## Other characteristics

- Lamp current: 145 mA

## Power consumption

- Power factor: >0.9
- Voltage: 220-240 V

## Product dimensions and weight

- Net weight: 0.25 kg
- Overall height: 44 mm
- Overall length: 152 mm
- Overall width: 152 mm
- Recessed Ceiling cutout: 14.4 cm x 14.4 cm

## Service

- Warranty: 2 year(s)

#### Technical specifications

- Diameter: 152 mm
- Total lumen output fixture: 1020
- Light color: 6500
- Mains power: 220–240
- Fixture dimmable: No
- Wattage bulb included: 8.5
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

#### Packaging dimensions and weight

- EAN/UPC – product: 8710619962638
- Net weight: 0.24 kg
- Gross weight: 0.35 kg
- Height: 7.5 cm
- Length: 15.2 cm
- Width: 15.2 cm



Issue date: 2025-09-03  
Version: 0.240

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)