



Comfortable light with a slimmer fit

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

Easy to experience

• Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Premium quality

- Durable and impact resistant die-cast aluminum housing
- EyeComfort light that's easy on the eyes

Durability

· Long life span up to 30,000 hours

Highlights

Suitable for low ceilingsSlim design Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: Round

Design and finishing

Color: WhiteMaterial: Plastic

Durability

Lumen maintenance factor: 70%

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

- · Color consistency: 5 SDCM
- · Color rendering index (CRI): 80
- · Color temperature: 2700 K
- · Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 77 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Garage
- Style: Contemporary
- Type: Ceiling Lights

Other characteristics

· Lamp current: 280 mA

Power consumption

· Voltage: 220-240 V

Product dimensions and weight

Overall height: 30 mmOverall length: 164 mmOverall width: 164 mm

Service

Warranty: 2 year(s)

Technical specifications

· Diameter: 164 mm

· Total lumen output fixture: 900

Flotal turner output fixture: 900
Light color: 2700
Mains power: 220
Fixture dimmable: No
Wattage bulb included: 12
IP code: IP20 | Finger-protected
Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8718696167823

Net weight: 0.29 kgGross weight: 0.39 kgHeight: 198 mmLength: 41 mm

· Width: 198 mm



© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips

