

# PHILIPS

Downlight

Functional

Astra Metallica

White

8718696168936



## Durable and bright

Philips premium Slim LED panel light with Aluminum housing for long life and bright light

### Match your interior

- Super slim design

### Light effect

- Bright light with uniform distribution
- Bright and even light

### Premium quality

- Durable and impact resistant die-cast aluminum housing
- EyeComfort - light that's easy on the eyes

### Material & finishing

- Durable aluminum housing

### Durability

- Long life span up to 25,000 hours

# Highlights

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Bright and even light

Light is clear and distributed evenly around your space in a dependable manner.

## Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

## Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Design and finishing

- Color: White
- Material: Metal

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional
- EyeComfort: Yes

## Product dimensions and weight

- Net weight: 0.158 kg
- Cut out length: 8.2 cm
- Cut out width: 8.2 cm
- Height: 1.8 cm
- Length: 11 cm
- Width: 11 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 110 mm
- Total lumen output fixture: 500
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 5
- IP code: IP20
- Class of protection: Class II

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696168936
- Net weight: 0.15 kg
- Gross weight: 0.2 kg
- Height: 16.2 cm
- Length: 14.4 cm
- Width: 3.3 cm
- Material number (12NC): 929001951846



Issue date: 2024-07-25  
Version: 0.368

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)